

- Part number : 27102 PRE
- Body : Composite
- Nozzle : Composite
- Triger : Progressive
- Insert : 1/4 BSP female metal thread
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Non scratch body
- Crush resistant
- Flow @ 6 b : 15 m³/h - 8.8 cfm
- Sound level : 84 db
- Nozzle lenght : 59 mm - 2.32 in
- Blowing force : 312 g
- Dynamic pressure : 2 b
- Weight : 116 g

