

## MNX ABS 150/60 HG



Sample photo

**Order symbol:** ABS 150/60 HG  
**Product nbr:** 6081313  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074022936  
**El. number:**  
 Finland 3420551  
 Denmark 8212023262  
 Italy 7361090  
 Sweden 2535751

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	L	W	H	Rating:
mm:	180	130	60	<b>Electrical insulation:</b> Totally insulated
inch:	7.1	5.1	2.4	<b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes

Materials:	
<b>Material:</b>	ABS
<b>Gasket material:</b>	TPE
<b>Base colour:</b>	RAL 7035
<b>Cover colour:</b>	RAL 7035
<b>Cover screws material:</b>	Polyamide
<b>Cover screws colour:</b>	Grey

**Electrical insulation:** Totally insulated  
**Halogen free (DIN/VDE 0472, Part 815):** Yes  
**Flammability Rating (UL 746 C 5):** UL 94 HB  
**Glow Wire Test (IEC 695-2-1) °C:** 650  
**NEMA Class:** NEMA 1, 4, 4X, 6  
**Ingress Protection (EN 60529):** IP 66/67  
**Impact Resistance (EN 50102):** IK 07

Temperatures:	
<b>Short term:</b>	-40 ... 80 °C
<b>Continuous:</b>	-40 ... 60 °C
<b>Short term:</b>	-40 ... 175 °F
<b>Continuous:</b>	-40 ... 140 °F

Certificates:
Fimko
Europe EN 50298: 1998
Gost R

Accessories:	
MIV 150	Mounting plate (Galvanized steel)
MIN 10	DIN-15 Mounting rail
MIN 15	DIN-15 Mounting rail
MIV 10	DIN-35 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 150/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

