

Datasheet

RS Pro Crimp Tool Die, Terminal, Terminal, Wire size 95 to 120 mm²

RS Stock No: **624-1336**



Product Details

RS Pro robust hydraulic crimper tool die is compact and ideal for working in confined spaces. Having the benefit of spring loaded handles, the dies can be advanced using only one hand, therefore leaving the other hand free to position the connector. It has a built in safety valve and pressure release lever for safety handling. This crimping tool die is housed in a moulded plastic carry case.

Features and Benefits

- Robust hydraulic crimping tool
- Compact and ideal for working in confined spaces
- 180° rotational head
- Supplied with Die Sets
- Built in safety valve
- Pressure release lever
- Housed in a moulded plastic carry case
- Comprehensive instructions included
- Crimping Force: 50 kN
- Rated operating pressure: 600 bar (8600 psi)



Specifications:

Connector Type	Terminal
Crimp Connector Type	Terminal
Maximum Wire Size (mm ²)	120 mm ²
Minimum Wire Size (mm ²)	95 mm ²
Terminal Insulation	Non-Insulated
Wire Size	95 to 120 mm ²