

Metal Circular Saw LXT®

DCS552

18V • 136 mm • 3 600 min⁻¹

Compact saw for easy, almost spark-free cutting of metal

Circular metal saw with fixed chip collection box for quick, almost spark-free cutting of metal. It is an ideal tool for electricians and air-conditioning and roofing fitters. Compatible with a blade with a 136 mm diameter that achieves a max. cutting depth of 50 mm.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3600 min ⁻¹
Max. Cutting Depth at 90°	50,5 mm
Electronic brake	✓
Blade Diameter	136 mm
Bore Size (Arbor Diameter)	20 mm
Sound Power Level (L _{WA})	113 dB(A)
Sound Pressure Level (L _{pA})	105 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²
Product Dimensions (L x W x H):	348 x 196 x 203 mm

User benefits

- Cutting metal quickly and without sparks.
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

■ Optional AC

B-33526

Circular Saw Blade, Specialized, TCT,



B-69303

Circular Saw Blade, Efficut, T.C.T,



B-69319

Circular Saw Blade, Efficut, TCT,



■ Other

User manual

Parts drawing