

TECHNICAL SHEET
KOFPRO841



Length (mm)	Width (mm)	Height (mm)	Maximum load dynamic capacity (kg)	Maximum load static capacity (kg)	Capacity (L)	Weight (kg)
800	400	550	90	90	176	11.5

Made of : polyethylene
Colors : grey

Range: STORAGE
Custom: 3923100000
EAN : 3321360021724

Others :

- Industrial chest
- Stackable up to 5
- Feet for piling them on the top of each other
- 100% waterproof, can be washed
- Closed with polyamide handle and integrated locks
- Comfortable built in handles on each side
- Food approved, Food items can be keep up to 12 hours with ice
- Temperature -40 / +80°
- Acid, grease and base resistant
- UV protection
- 2 years guaranty
- All types of KOFPRO are with EURO dimensions fitting Europalets
- Wheels diameter 125 mm
- Pulling handle

