



ROLLED KNUCKLE CONTINUOUS HINGE - 80 MM WIDTH

42-1-3304

Opening angle 270°. Other lengths and pin materials are available on request.
Specific drilling requirements are also available on request.

A	1000 mm
Note	undrilled

Material	304 stainless steel
Weight (g)	2530 g
B	80 mm
C	3 mm
E (knuckle or thickness)	40 mm
D (pin diameter)	6
Finish	raw
Pin material	stainless steel

