



ENGLISH

Datasheet

136-8578 CT700 TRACER/TONER/CABLE TESTER



RS Article No.	Body type	Kind of Cable Tester	Conditions of Cable Tester	Display	Operating way	Battery type
136-8578	Plastic	LAN, TEL, COAX	PASS, OPEN, SHORT.	LED Indicator	Tact Switch Keypad	Alkaline 9VDC



SPECIFICATIONS:

Display:	LED Indicator
Connector Type:	RJ45, Alligator Clip(Red, Black), BNC connector
Cable Type:	LAN, TEL, COAX, Bare wire...
Error Status:	OPEN, SHORT.
Toner/Tracer:	Toner Output (0~5V) Pulse, Prober Sound Output (Max:108dB).
Length for Test:	1~350 meters (3~1200 feet)
Power Source:	9VDC Battery.
Operating Temperature:	0° to 50° C (32° to 122° F)
Storage Temperature:	-10° to 60° C (14° to 140° F)
Humidity:	10 % to 90 % non-condensing
Dimension:	Amplifier Probe : 230(L) x 60.3(W) x 28(H) mm Tone Generator : 104(L) x 70(W) x 36(H) mm
Certification:	CE, RoHS