



Product-Nr.	156510-11
EAN:	4260556627434
Model:	TUBELED_70 EVO AC
Order number:	156510-11
Model:	TUBELED_70 EVO AC
Illuminant:	SMD LED
Total output incl. driver:	81 W
Power consumption:	74 W
Lamp luminous flux:	11394 lm
Lamp luminous efficiency:	155 lm/W
Light colour:	5600K 3-step MacAdam
Number of poles:	3
Connected load:	120-277V AC, 50 - 60 Hz
Power supply:	integrated
Connection (connector):	M12 S-coded
Degree of protection:	IP67/IP69K
Class of protection:	I
Glare control:	diffuser film
Beam angle (optics):	100°
Operating temperature:	-20 °C - +60 °C (-4 °F - 140 °F)
Storage temperature:	-20 °C - +80 °C (-4 °F - 176 °F)
Colour rendering (Ra):	>85
Lamps lifetime:	> 100,000 h (L80/B10)
Housing material:	Aluminum, glass
Height [B] x Width [C]:	59,5 mm x 70 mm (~2,34" x ~2,76")
Length [A]:	1580 mm (~62,2")
Weight (net):	4400 g (~155 oz)
Gross weight:	5830 g (~206 oz)
Risk group (DIN EN 62471):	free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	no
Mounting accessories:	optional
Made in:	Germany