



Main

Range	Actassi
Product	Vertical ring
Product destination	Rack 600 mm wide
Additional features	Openable

Complementary

Number of rack unit	1U
Maximum capacity	48
Material	Metal sheet: DC01 1.2 mm Strap: velcro
Colour	Dark grey (RAL 7016)
Width	0.300 M 30 mm
Height	0.40 M 40 mm
Depth	0.40 M 40 mm

Environment

Temperature range	-10...55 °C 14...131 °F
-------------------	----------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations