

Eaton 12FDLNJ31.5

Catalog Number: 12FDLNJ31.5

Eaton Bussmann series medium voltage DIN fuse, 31.5 A, AC 12 kV, 2", 51 x 292 mm, fullrange, DIN

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	12FDLNJ31.5
	EAN 5027590432306
Product Length/Depth	Product Height
360 mm	51 mm
Product Width	Product Weight
51 mm	1613.333 g
Compliances	Certifications
DIN 43625 VDE 0670-4	IEC60282-1

Electrical data

Amperage Rating

31.5 A

Voltage rating

12 kV

Voltage type

AC

Breaking capacity

50 kA

Performance Cat According To IEC 60282-1

Full-range

Rated frequency - min

50 Hz

Class

Class full-range

Product specifications

Fuse indicator

Non Indicating

Construction size

51 x 292 mm

Standard

DIN

Standard

DIN

Resources

Catalogues

[Medium voltage fuse-links](#)

Technical data sheets

[720106 24kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia