

Adapter - EM-CPS-DA-18S/16A-L1 - 1089439


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Single-position adapters with CrossLink® interface for connecting miniature circuit breakers, 16 A, phase L1, with one fixed DIN rail, with conductors AWG 14 (2.5 mm²)



Key Commercial Data

Packing unit	6 pc
Minimum order quantity	6 pc
GTIN	 4 055626 892641
GTIN	4055626892641
Weight per Piece (excluding packing)	58.630 g
Custom tariff number	85369095
Country of origin	Germany
Sales Key	CK78Z1

Technical data

General

Rated voltage	690 V AC (IEC)
	600 V AC (UL)
Rated current	16 A (IEC)
	16 A (UL)

Standards and Regulations

Standards/regulations	IEC 61439-1
	GB/T 7251.1
Rated insulation voltage	800 V AC
Rated surge voltage	6 kV

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
------------	--

Adapter - EM-CPS-DA-18S/16A-L1 - 1089439

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 11.0	27371392
eCl@ss 9.0	27379201

ETIM

ETIM 6.0	EC002498
ETIM 7.0	EC002498

Approvals


Approvals


Approvals


UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
-----------	---	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
------------	---	---	---------------

cULus Listed			
--------------	---	--	--