

Features

- 64 Selectable tones
- 105dB Sound Level
- Operating Temperature -40°C to +55°C
- IP65 Rated
- Polycarbonate plastic offering protection against UV and is Impact resistant

RS PRO MULTI CHANNEL ELECTRONIC SOUNDER 105DB 12-24VAC/DC

RS Stock No.: 0726242



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Introducing the range of RS PRO Electronic Sounders, ideal audible signalling units offering high-frequency sound output like a siren or klaxon for warnings and emergencies. The beacons are electromechanical sounder units that can be fitted in a wide variety of environments to be used as clear signals that ensure the safety of workers as well as ensure safe and essential day-to-day operation of expensive machinery and parts, reducing unplanned downtime and risks of damage or injury. The sounders are available in a range of frequencies and are versatile enough to be used within factories and manufacturing plants, construction areas and numerous public areas.

General Specifications

Lens	Polycarbonate
Sound output	105dB at 1M
Multi tone	Yes selectable via dip switch
Colour	Grey
Fitting	Screw
Protection	Vibration CEI 60068-2-6

Electrical Specifications

Supply Voltage	12-24VAC/DC
Current Type	AC or DC
Current Consumption	85mA-12VDC, 60mA-24VDC, 280mA-12VAC, 190mA 24VAC

Mechanical Specifications

Dimensions	92 (d) x 102mm (h)
Base Diameter	92mm
Mounting Style	Screw Mount
Weight	0.34kg

Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+50°C

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	CE / CSA / UL94-V0
Standards Met	EMC (ECE R10), RoHS Compliant