

41RM



Ratchet flex combination wrenches

- Ratchet combination wrenches with swivel head in metric sizes
- Standards: ISO 3318 and DIN 3113
- Material: High performance alloy steel
- Open end angle 15° with a slimmer head to get more accessibility
- Ratchet swivel head in 180° with fixed steps in every 15°
- 5° ratchet action angle
- 12 points Dynamic-Drive Profile provides longer life for screws and nuts
- Chrome plated Micro Matt finishing provides high quality surface



				L mm	a1xa2 mm	b1xb2 mm	
41RM-8	7314153014412	1	8	127	6,5x4,3	17,0x17,0	35
41RM-10	7314153014429	1	10	136	7,3x5,0	20,0x21,0	55
41RM-11	7314153014436	1	11	141	7,7x5,4	22,0x23,0	63
41RM-12	7314153014443	1	12	148	8,2x5,8	23,0x25,0	83
41RM-13	7314153014450	1	13	154	8,6x6,1	25,0x27,0	93
41RM-14	7314153014467	1	14	160	9,0x6,4	27,0x29,0	113
41RM-17	7314153014474	1	17	190	10,3x7,6	32,0x36,0	173
41RM-19	7314153014481	1	19	215	11,2x8,6	34,0x40,0	233
41RM-21	7314150219742	1	21	274	13,0x9,0	40,0x46,0	393