



B195PH

BahcoFit Stubby Phillips Screwdrivers with Rubber Grip PH1-PH2










PRODUCT DETAILS

- For Phillips head screws, stubby-type for working in confined spaces
- Black oxide tip for higher accuracy
- Two-component handle for comfortable grip and high torque transfer
- Markings on the handle for quick identification of the tip
- Integrated hanging hole
- Chrome plated blade for high protection against corrosion, long life tool
- High-performance alloy steel blade
- Standards: ISO 8764/DIN 5260
- SB coding retailed packed on a plastic hanger



PRODUCT ATTRIBUTES

Product							
B195.001.025	PH1	25 mm	5 mm	33 mm	60 mm	85 mm	40 g
B195.002.025	PH2	25 mm	6 mm	33 mm	60 mm	85 mm	40 g
SB195.001.025	PH1	25 mm	5 mm	33 mm	60 mm	85 mm	44 g
SB195.002.025	PH2	25 mm	6 mm	33 mm	60 mm	85 mm	44 g

Follow the Fish!

