

Features

- Aluminum indicator
- Stainless steel pan
- Large LCD display
- Hold and Tare function.
- Simple and convenient operation
- Weighing units (kg, lb, pcs)
- Wall mount for display device standard
- USB port

RS PRO Platform Weighing Scale, 30kg Weight Capacity

RS Stock No.: 0212378, 0212380, 0212381,
0212382, 0212383



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Platform Weighing Scale

RS PRO professional platform scale ideal for strong, sturdy daily weighing applications.

- Aluminium indicator
- Stainless steel platform
- Large LCD display
- Hold and Tare function
- Mains adaptor
- Wall mount for display device standard
- Simple and convenient 4-key operation
- USB port

General Specifications

Weighing Capacity	30kg
Scale Type	Platform
Resolution	10g
Plug Type	Type A - North American/Japanese 2-blade, Type C - European Plug, Type G - British 3-pin, Type I - Australian plug
Weighpan Length	315mm
Weighpan Width	280mm
Weighpan Height	45mm
Net Weight	2.8kg
Minimum Operating Temperature	0°C
Maximum Operating Temperature	40°C

Electrical Specifications

Tolerances	±3d
Product Material	Stainless steel housing + Aluminium indicator
Function	Hold and Tare function
Weighing Units	Kg.lb, pcs
Power Requirement	4 x AAA Batteries (not included) or adaptor (included)

Approvals

Certification	CE
Declarations	REACH DoC

Similar Products

Stock No.	Brand	Product Name	Weight Capacity	Resolution	Weighpan Dimension
0212398, 0212399, 0212400, 0212401, 0212403	RS PRO	Platform Weighing Scale	30 kg	10g	315 x 280 x 45mm
0212384, 0212386, 0212387, 0212388, 0212390	RS PRO	Platform Weighing Scale	60 kg	20g	315 x 280 x 45mm
0212392, 0212393, 0212394, 0212396, 0212397	RS PRO	Platform Weighing Scale	150 kg	50g	315 x 280 x 45mm