

Datasheet

RS Pro Stainless Steel Countersunk Head Machine Screws, M6 x 16mm

RS Stock No: **914-1810**



Product Details

RS Pro machine screw measuring M6 x 16 mm, is made of type 304 S15 A2 grade 18/8 stainless steel. The countersunk head screw with metric thread, can be used at up to 800°C. The cross drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- Countersunk head screw, metric thread
- A2 grade 18/8 stainless steel (Type 304 S15) construction
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

**Specifications:**

Drive Type	Pozidriv
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	16 mm
Stainless Steel Type	304 (A2)
Thread Pitch	1
Thread Size (Metric)	M6
Head Diameter	10.87 to 11.3 mm
Head Height	3.3 mm
Recess Diameter	3 to 3.45 mm
Specification	DIN 965