



Foot protection

ESKIMO SBHP SR

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

Canadian safety boot specially designed for use in outdoor cold conditions or in cold rooms with temperatures as low as -30°C



Specific benefits



Comfort

- Shock-absorbing heel to relieve joint strain
- Padded collar for comfort and ankle support



Performance

- Construction of the model for great insulation against the cold
- Waterproof design prevents water penetration
- High stability ensured by the sole's grip properties
- Sole with specific PU resistant to -30°C

Certifications and norms



EN ISO 20345

SB CI WR FO A E PS CR SR



DELTA-TEX WATERPROOF

Applications

- Agriculture
- Public works
- Building
- Finishing works / Craftsmanship
- Events & scenic
- Public services

Protects against risks



Antistatic



Shock



Cold



Slip



enjoy safety.

Edit 15/12/2024
www.deltaplus.eu



Foot protection

ESKIMO SBHPSR

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

Canadian safety boot specially designed for use in outdoor cold conditions or in cold rooms with temperatures as low as -30°C

Standards - Details

Technical details

Shoe type	Half-boot
Outsole material	PU, 2d
Anti-perforation insert	Metal free
Upper material	Leather, Textile, Polyester
Upper finition material	Grain Leather, PU deeped
Upper height size 42 (cm)	27
Calf circumference (cm)	44
Safety toe-cap	Composite
Lining material	Membrane, Polyester, Synthetical-fur, Delta-Tex
Lining material finition	Isotermic
Footbed material	Felt
Footbed caracteristic	Ergonomic, Removable
Outsole finition	Injected
Weight (g per shoe)	865
Size range	38 → 48








Safety footwear

ESKIMO SBHPSR

INDUSTRY-CONSTRUCTION & CIVIL ENGINEERING

Canadian safety boot specially designed for use in outdoor cold conditions or in cold rooms with temperatures as low as -30°C

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
ESKIMSHNO38	Black	38	ESKIMO SBHP SR	3295249198305	13295249198302	5	1	10.0 kg	35.5 cm	64.0 cm	39.5 cm
ESKIMSHNO39	Black	39	ESKIMO SBHP SR	3295249190798	13295249190795	5	1	10.0 kg	35.5 cm	64.0 cm	39.5 cm
ESKIMSHNO40	Black	40	ESKIMO SBHP SR	3295249190804	13295249190801	5	1	11.0 kg	35.5 cm	64.0 cm	39.5 cm
ESKIMSHNO41	Black	41	ESKIMO SBHP SR	3295249190811	13295249190818	5	1	11.0 kg	35.5 cm	64.0 cm	40.5 cm
ESKIMSHNO42	Black	42	ESKIMO SBHP SR	3295249190828	13295249190825	5	1	11.0 kg	35.5 cm	64.0 cm	40.5 cm
ESKIMSHNO43	Black	43	ESKIMO SBHP SR	3295249190835	13295249190832	5	1	12.2 kg	37.5 cm	66.0 cm	41.5 cm
ESKIMSHNO44	Black	44	ESKIMO SBHP SR	3295249190842	13295249190849	5	1	12.2 kg	37.5 cm	66.0 cm	41.5 cm
ESKIMSHNO45	Black	45	ESKIMO SBHP SR	3295249190859	13295249190856	5	1	12.2 kg	37.5 cm	66.0 cm	41.5 cm
ESKIMSHNO46	Black	46	ESKIMO SBHP SR	3295249190866	13295249190863	5	1	13.6 kg	41.5 cm	69.0 cm	44.0 cm
ESKIMSHNO47	Black	47	ESKIMO SBHP SR	3295249190873	13295249190870	5	1	13.6 kg	41.5 cm	69.0 cm	44.0 cm
ESKIMSHNO48	Black	48	ESKIMO SBHP SR	3295249198312	13295249198319	5	1	13.6 kg	41.5 cm	69.0 cm	44.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height