



PRODUCT-DETAILS

UPS PowerValue 11T G2 1 kVA B

UPS PowerValue 11T G2 1 kVA B



General Information	
Extended Product Type	UPS PowerValue 11T G2 1 kVA B
Product ID	4NWP100160R0001
EAN	7640169261886
Catalog Description	UPS PowerValue 11T G2 1 kVA B
Long Description	VFI online double conversion;900W;8.5min;RS232;USB;mini COM slot

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD005611
RoHS Information	4NWD005610 rev.B
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	d4a7c838-eac3-4acf-bf4f-7f8776acb903 Switzerland
Simplified SCIP	01a551ce-74c8-48eb-ac97-ffffd9d51510 Norway 9b729f3b-bbbc-4a2a-89aa-a55e7925ba8e Croatia 954b32eb-505e-4257-aa31-360a735ca50b Germany b0730bb6-6f60-4bed-ae99-7fcd2f30144e Denmark d2e1985a-d23c-4e3c-8db3-f2591d01cbe7 Germany 9d493652-7b15-4f3c-bea5-0bd411ee159b Germany

92f02ef1-f40c-475c-8b95-942218e7178d	Sweden
4e207d4e-6c35-40b4-8546-d6afc5529a8e	Germany
76bd9f12-15a4-42c3-9a07-82d2ce588161	Estonia
a10770f0-c28d-433d-ae9-d8fc5723b6cf	Finland
ef25630c-a2a4-4d6d-8c29-afb9a7c2aa83	Germany
be8dbcc9-0455-4f12-946b-9aa165ef662a	Sweden
1cd48341-93bf-425c-b2a3-83be3ffac0fe	France
dd383f3e-d53c-43e1-bd81-0977a1f9d1aa	Poland
f6ae7241-7db5-4748-83d6-90c203605920	Belgium
ea784466-757e-40e6-a17e-ad93e61b43be	Greece
39d60a55-981c-41e8-a109-4bf52dc14f2b	Portugal
4e5f1432-929d-4196-ab4b-338aec2d9a79	Bulgaria
2ef1c400-59b0-4d0d-9f59-299523b280c0	Belgium
6b9321a7-5d67-4a0c-a61b-376f0fe655a6	Czech Republic
c13d6f2b-a13e-4bfb-93b0-ed59cc5b7b8a	Hungary
153d9bd9-e9f2-4153-991d-1e8143b1300e	Poland
76ac568d-60e2-4ff5-b2ca-a4e37b0885cd	Netherlands
d103bae0-8869-432f-aac8-7200d62c3cc1	Spain
2732acca-9562-449e-8338-d447ac5ab916	Hungary
0a1e4b1f-7150-446e-920c-039e0c3709f6	France
1b379d07-4fe8-4328-81bd-4476700c23d0	Poland

Popular Downloads

Data Sheet, Technical Information	4NWD003883_EN
Instructions and Manuals	4NWD003883_EN

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408610
E-Number (Norway)	6609400
E-Number (Sweden)	5257245
Country or Territory of Origin	China

Dimensions

Product Net Width	144 mm
Product Net Height	228 mm
Product Net Depth / Length	356 mm
Product Net Weight	9.3 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	240 mm
Package Level 1 Height	330 mm
Package Level 1 Depth / Length	436 mm
Package Level 1 Gross Weight	10.3 kg
Package Level 1 EAN	7640169261886

Technical

Apparent Power Output	1000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U _{in})	220 V 230 V 240 V
Input Voltage Type	AC
Number of Batteries	4
Number of Outputs	C13 Connection 4
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function Potential free switch contact Network-management
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	900 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004828

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 T G2 IEC 230V

