



AIR HOSE HP 9.5X15 MM

RR7045

RR704...

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>





DESCRIPTION

AIR HOSE HP 9.5X15 MM

These hybrid polymer compressed air hoses are wear-resistant and flexible. They are ideal for use with a hose reel a hose reel and for use with pneumatic tools. They have an internal diameter of 9.5 mm and an external outer diameter of 15 mm. These air hoses are also resistant to oil, petrol, grease, light acids and alkalis. acids and alkalis.

Lengths :

RR7040: 15 Metres

RR7043 : 23 Metres

RR7045 : 30 Metres

Air inlet: 3/8".

Maximum working pressure: 300 PSI.

EXTREMELY FLEXIBLE - flexible in all weather conditions (-40°C to 80°C).

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>



VERY DURABLE - thoroughly tested for hose rupture and coupling.

PERFECTLY COATED - High quality hose coating for maximum protection.

SPECIFIC DATA

Designation	AIR HOSE PU 9,5X12MM 30 METERS
Sales reference	RR7045
Weight (kg)	3.600
Guarantee	C

Guarantee applied**C | Consumable**

The products in this category will not be replaced and are subject to normal wear phenomena.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

