

Datasheet

RS Pro 1550 Series 3.81mm Pitch Straight PCB Terminal Block with Plug In Termination, Screw, 2 Way

RS Stock No: 874-5063



Features and Benefits

- Right angle cable mount terminal block plug connectors feature a 3.81 mm pitch, M2.5 screw flanges and a 300 V 8 A electrical rating
- These 3.81 mm cable mount pluggable terminal blocks have M2 rising cage clamp screw terminals that accept a wire size range of 28 to 14 AWG and green PBT housings
- Nylon 66 construction

Specifications:

Body Orientation	Straight
Colour	Green
Current Rating	8 A (UL), 10 A (IEC)
Depth	11.1 mm
Gender	Female



ENGLISH

Length	18.21 mm
Material	Nylon 66
Mounting Type	Screw
Number of Contacts	2
Number of Rows	1
Pitch	3.81 mm
Termination Method	Plug In
Type	Plug
Voltage Rating	300 V (UL), 250 V (IEC)
Width	15.6 mm
American Wire Gauge	16 to 28 AWG
Insulation Withstands Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ
Flammability Rating	UL 94 V-0