



DX4 DETACHABLE HOLSTER POCKET TROUSERS

DESCRIPTION

The DX4 Holster Trousers are ergonomically designed and use the targeted placement of dynamic 4X stretch fabrics to give maximum range of movement when working. The trousers feature a high-rise back waistband with side elastication, ensuring protection in all working positions. Pre-bent top loading adjustable knee pad pockets, generously sized front pockets and multi-functional zip thigh pockets offer secure storage of phone, pens and tools. Triple stitching throughout for maximum durability.

COMPOSITION

- Titanmill Pro Stretch: 93% Polyester, 7% Elastane, 270g**
- 65% Polyester, 35% Cotton Ripstop Weft Stretch, 230g**
- CorePro: 87% Nylon, 13% Elastane, 245g**
- Metal Grey 28-48**

FEATURES

- 4-way stretch fabric for ease of movement and added comfort
- High rise back waistband ensures protection in all working positions
- Reflective trim for increased visibility and safety
- Zip off holster pockets for added versatility
- Two tier knee pad pockets allowing two positioning options
- Multiple side zip compartments for secure storage
- 16 pockets for ample storage
- 2 side zip pockets for secure storage
- Smart phone pocket
- Hammer loop for secure storage of work tools
- 2 Back pockets
- 2 Zipped thigh pockets

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
DX440MGR	METAL GREY	28-14

FEATURES



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



16 POCKETS
16 pockets for ample storage



DYNAMIC 4X STRETCH

What defines this collection is its cutting edge slim fit design, high performance stretch fabrics and clever innovations ensure the wearer achieves maximum function, comfort and style.

GET THE COLLECTION



TECHINCAL INFORMATION



- Do not iron the reflective tape
- Wash dark colours separately
- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash reflective tape on the inside
- Wash with similar colours

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m ³)	EAN13	GTIN/DUN14
DX440MGR28	Metal Grey	65	45	36	1.147	5850.000	5036108326105	15036108814883
DX440MGR30	Metal Grey	65	45	36	1.165	5850.000	5036108326112	15036108814890
DX440MGR32	Metal Grey	65	45	36	1.140	5850.000	5036108326129	15036108814906
DX440MGR33	Metal Grey	65	45	36	1.140	5850.000	5036108326136	15036108814913
DX440MGR34	Metal Grey	65	45	36	1.181	5850.000	5036108326143	15036108814920
DX440MGR36	Metal Grey	65	45	36	1.207	5850.000	5036108326150	15036108814937
DX440MGR38	Metal Grey	65	45	36	1.190	5850.000	5036108326167	15036108814944
DX440MGR40	Metal Grey	65	45	36	1.238	5850.000	5036108326174	15036108814951
DX440MGR41	Metal Grey	65	45	36	1.262	5850.000	5036108326181	15036108814968
DX440MGR42	Metal Grey	65	45	36	1.230	5850.000	5036108326198	15036108814975
DX440MGR44	Metal Grey	65	45	36	1.290	5850.000	5036108326204	15036108814982
DX440MGR46	Metal Grey	65	45	36	1.307	5850.000	5036108326211	15036108814999
DX440MGR48	Metal Grey	65	45	36	1.270	5850.000	5036108326228	15036108815002