

2-Port HDMI KVM Switch with Built-In Cables - USB 4K 60Hz

Product ID: SV211HDUA4K



The SV211HDUA4K 2-Port 4K60Hz HDMI Cable KVM Switch with Audio and Remote Switching Control gives you control of two HDMI, USB equipped computers with a single monitor, keyboard, mouse and audio peripheral set.

4K60 Picture & Full Audio Support

The Dual HDMI KVM switch supports resolutions up to 4K at 60Hz and can drive one large HDMI display with ease, maximizing viewing space. With support for separate 3.5 mm stereo audio, the KVM switch delivers full audio compatibility across connected computers.

OS Independent

While supporting most PC operating systems, this HDMI KVM switch is OS independent which means it works with Mac computers (an adapter may be required) and any other laptops, notebooks, and tablets.

Simple to Operate

The switch features a remote push-button on a 1.5 meter (4ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac® compatible software for switching between systems.

StarTech.com KVM Switches & Consoles

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

The SV211HDUA4K is backed by a 2-year StarTech.com warranty and free lifetime multilingual technical support.

Certifications, Reports and Compatibility



Features

- Operate and access two HDMI computers from one workstation at 4K 60Hz resolutions
- Integrate into your set up quickly and easily with built-in 4 ft. KVM cables (including remote switch) and a space-saving design
- Switch PCs via push-button, hot-keys or switching software
- Switching software supports Windows, Windows Server & macOS platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio Analog (3.5mm) and HDMI audio supported

Hardware	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	HDMI
	Rack-Mountable	No
Performance	Audio Specifications	Two Channel Audio Input and Output
	Auto Scan	10, 20, 30, 40, 50, and 60 seconds
	Hot-Key Selection	Yes
	IP Control	No
	Maximum Data Transfer Rate	480Mbps (USB 2.0)
	Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz
	MTBF	1,012,884 hours
	On-Screen Display	No
	Port Selection Support	Push Button, Hotkeys, and Software
	Wide Screen Supported	Yes
Connector(s)	Console Interface(s)	2 - USB Type-A (4 pin) USB 2.0 Receptacle 1 - HDMI Receptacle 2 - 3.5 mm Mini-Jack (3 Position) Receptacle
	Host Connectors	2 - USB Type-A (4 pin) USB 2.0 Plug 2 - HDMI Plug 4 - 3.5 mm Mini-Jack (3 Position) Plug
Software	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.6 to 10.9
Special Notes / Requirements	Note	In order to access the software and hotkeys of the KVMs, a compatible OS must be installed on the connected host, however the KVM and push button switching function is OS independent
Indicators	LED Indicators	2 - Orange
Power	Power Source	Bus Powered

Environmental	Humidity	0 ~ 90% RH, Non-Condensing
	Operating Temperature	0 ~ 40C
	Storage Temperature	-20 ~ 60C
Physical Characteristics	Product Height	25.000
	Product Length	52 in [132 cm]
	Product Width	97.000
	Weight of Product	431.000
Packaging Information	Package Height	63.000
	Package Length	160.000
	Package Width	250.000
	Shipping (Package) Weight	522.000
What's in the Box	Included in Package	1 - KVM Switch
		1 - Quick-Start Guide

Product appearance and specifications are subject to change without notice.