



ENCLOSURE: IP67
 TORQUE: 3Kg.m
 OPERATION TIME: 12sec
 POSITION SWITCH: 4 SPDT SWITCH
 CABLE ENTRY: PG 11 x 1
 MOUNTING FLANGE: F03/F04/F05
 acc to DIN/ISO5211

