



Chemical protection

ULTRANITRIL 458

Frequent contact | intermittent wear



ADVANCED GRIP
TECHNOLOGY

CHEMICAL PROTECTION
TYPE A

EN 388



4X01X

EN 374-1



Type A
AJKOPT

EN 374-5



VIRUS

EN ISO 18889



G2

EN 421



Dexterity EN ISO
21420: 5/5

CATEGORY 3



0334

Designed with an embedded optimal grip to safely handle tasks in dry & greasy environments

SPECIFIC ADVANTAGES



Comfort

- Very supple glove providing high dexterity
- Good fingertips sensitivity



Durability

- Long service life: excellent mechanical resistance (abrasion)



Productivity

- Optimal grip to improve productivity, reduce hand fatigue and enhance safety



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Recycled material in the packaging: 30 %

INDUSTRIES

- Agriculture sector
- Automotive industry
- Chemical industry
- Laboratory
- Metallurgy
- Food industry
- HEALTH CARE:
Pharmaceutical industry

APPLICATIONS

- Spray mixtures preparation
- Pesticides handling
- Tank filling
- Application & spreading of pesticides
- Pesticides waste management
- Treatment equipment cleaning
- Mechanical maintenance
- Chemical product blending
- Handling and transport of chemical products
- Automotive assembly



Chemical protection

ULTRANITRIL 458

Frequent contact | intermittent wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
4 X 0 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	A: Methanol
TYPE A	J: n-Heptane
	K: Sodium hydroxide 40%
	O: Ammonia 25%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
	PROTECTION FROM PESTICIDES
G2	G2: Diluted & concentrated pesticides / Mechanical risk
ISO 18889	
EN 421	RADIOACTIVE CONTAMINATION
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria, fungi and virus
VIRUS	

PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Reinforced grip
Material	Nitrile
Colour	Green
Length (cm)	32
Thickness (mm)	0.50
Sizes	6 7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/bag 100 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/11/25/2716
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France