



Part Number : [1300390370](#)
Product Description : DeviceNet Trunk Male Terminator Resistor with Mini-Change Connection, without LEDs, 5 Poles
Series Number : 130039
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : DN100




Documents & Resources

Drawings
[1300390370_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	DeviceNet Trunk Male Terminator Resistor with Mini-Change Connection, without LEDs, 5 Poles
IP Rating	IP67
Product Name	DeviceNet Trunk
Type	Termination Resistor
UPC	78678869001

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	50V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	n/a
Net Weight	36.287/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0°C to +60°C

Wire Size (AWG)	N/A
-----------------	-----

This document was generated on Mar 27, 2025