

## 1100-1.04/12A

### Puller assortment inside/outside

in L-BOXX® 136

Code	ETIM
2927241	EC011834
EAN	UNSPSC
4010886945230	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-90-90
Customs tariff number	
82055980	



### Article description

- Max. capacity 3 and 5 t
- For clamping depths up to Ø 200 mm external, Ø 70-260 mm internal, and clamping reach up to 300 mm
- With 3 of 4 spindles the spindle tip can be turned (ball/tip)
- Quick-release pulling legs with integral T-profile for a better transmission of force
- 2 rigid extensions each 100 and 150 mm with leg brake for quick adjustment of the legs
- With Check-Tool insert for quick check of tool completeness
- No. 1100 CT2-1.04/12A for retrofitting existing L-BOXX®s 136
- As tools are fully sunk in the foam, the equipped insert can be stacked
- Insert can be used in drawers with minimum dimensions 400 x 310 x 90 mm

### Article parts list

Universal puller No. 1x 1.04/1A, 2-arm 130x100 mm ,Universal puller No. 1.04/2A 2-arm 200x150 mm ,Extension with hook brake No. 106/A-100-VB, 100 mm ,Extension with hook brake No. 106/B-150-VB, 150 mm ,Spindle No. 1.1406200 17 M14x1,5 200 mm ,Spindle No. 1.2106350KS, 22, G 1/2", 350 mm, with ball point ,+ GEDORE L-BOXX® 136 No. 1100 L

### Article information

Contents (Qty of pieces)	7	Total height [mm]	152 mm
reversible arms available	yes	Clamping width a2 (min.) internal pulling [mm]	70 mm
Net weight [kg]	9,6 kg	Clamping width a2 (max.) internal pulling [mm]	260 mm
Usable clamping reach [mm]	300 mm	Tractive force (max.) [t]	3 und 5
Clamping width (max.) external pulling [mm]	200 mm	Total depth [mm]	360 mm
Total width [mm]	444 mm		