



Sample photo

**Order symbol:** AL 234011  
**Product nbr:** 7011400  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074004277  
**El. number:**  
Finland: 3423641  
Denmark: 8212004838  
Italy: 7321110

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		401	230	110	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		15.8	9.1	4.3	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Material:</b>	Aluminium				<b>Certificates:</b> Underwriters Laboratories Fimko UL Canada Gost R
<b>Base colour:</b>	RAL 7001				
<b>Cover colour:</b>	RAL 7001				
<b>Cover screws material:</b>	Stainless steel				
<b>Gasket material:</b>	Neoprene				
<b>Temperatures:</b>					
<b>Short term:</b>	-50 ... 140 °C				
<b>Continuous:</b>	-50 ... 80 °C				
<b>Short term:</b>	-60 ... 285 °F				
<b>Continuous:</b>	-60 ... 175 °F				
<b>Accessories:</b>					
AM 2340	Mounting plate				
ARH 40	DIN-35 Mounting rail				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

