

Accessory LED lamp 025 DC connector for output side blue



Model		
product brand name		SIVACON
product designation		DC socket
design of the product		For output side, blue
type of light source		LED
Protection class		
protection class IP		IP20
Product details		
product component		
• ON/OFF switch	No	
• light sensor	No	
• socket outlet	No	
product feature magnetic		No
Connections		
type of electrical connection for through-wiring		Plug-in connection
Mechanical Design		
fastening method		miscellaneous
material		plastic
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information	
Information on the packaging	
https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information- and Downloadcenter (Catalogs, Brochures,...)	
http://www.siemens.com/lowvoltage/catalogs	
Industry Mall (Online ordering system)	
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2210-4A	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
https://support.industry.siemens.com/cs/ww/en/ps/8MR2210-4A	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)	
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2210-4A	
CAx-Online-Generator	
http://www.siemens.com/cax	
Tender specifications	
http://www.siemens.com/specifications	

