

Datasheet

RS Flanged Enclosure



Stock No.	Colour	Dimensions	Cable Diameter for Outlet
919-0326	Black	50 x 35 x 22 mm	2 core, 3 mm
919-0329	Black	50 x 50 x 17 mm	2 core, 3 mm
919-0323	Black	50 x 50 x 27 mm	2 core, 3 mm
919-0332	Black	70 x 50 x 17 mm	2 core, 3 mm
919-0335	Black	70 x 50 x 29 mm	2 core, 3 mm
919-0339	Black	70 x 50 x 42 mm	2 core, 3 mm
919-0348	Black	90 x 45 x 27 mm	2 core, 3 mm
919-0341	Black	105 x 70 x 20 mm	2 core, 6 mm
919-0345	Black	105 x 70 x 35 mm	2 core, 6 mm
919-0354	Black	105 x 70 x 50 mm	2 core, 6 mm
919-0357	Black	80 x 80 x 23 mm	2 core, 6 mm
919-0351	Black	80 x 80 x 43 mm	2 core, 6 mm
919-0360	White	50 x 35 x 22 mm	2 core, 3 mm
919-0363	White	50 x 50 x 17 mm	2 core, 3 mm
919-0367	White	50 x 50 x 27 mm	2 core, 3 mm
919-0376	White	70 x 50 x 17 mm	2 core, 3 mm
919-0379	White	70 x 50 x 29 mm	2 core, 3 mm
919-0373	White	70 x 50 x 42 mm	2 core, 3 mm
919-0382	White	90 x 45 x 27 mm	2 core, 3 mm
919-0385	White	105 x 70 x 20 mm	2 core, 6 mm
919-0389	White	105 x 70 x 35 mm	2 core, 6 mm
919-0398	White	105 x 70 x 50 mm	2 core, 6 mm
919-0391	White	80 x 80 x 23 mm	2 core, 6 mm
919-0395	White	80 x 80 x 43 mm	2 core, 6 mm