

# 25U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK25U



The 4POSTRACK25U 25U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 25U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

**Certifications, Reports  
and Compatibility**



**Applications**

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

**Features**

- 25U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Special Features	Adjustable Mounting Rails
		Base Plate with Floor-Anchoring Holes
		Built-in Cable Management
		Casters (Included)
Grounding Lug(s)		
Leveling Feet		
Easy Assembly		
U-Markings		
U Height	25U	
Wallmountable	No	
<b>Performance</b>	Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Maximum Mounting Depth	40 in [101.7 cm]
	Minimum Mounting Depth	22 in [56 cm]
	Product Height	47.8 in [121.3 cm]
	Product Height with Casters	50.8 in [129 cm]
	Product Length	3.4 ft [1 m]
	Product Width	23.8 in [60.4 cm]
	Weight of Product	72.9 lb [33 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Height	7.9 in [20 cm]
	Package Length	5 ft [1.5 m]
	Package Width	6.3 in [16 cm]

	Shipping (Package) Weight	77.4 lb [35 kg]
<b>What's in the Box</b>	Included in Package	<ul style="list-style-type: none"> <li>2 - Left Vertical Rail</li> <li>2 - Right Vertical Rail</li> <li>2 - Base Bracket</li> <li>8 - Corner Section</li> <li>4 - Center Section</li> <li>2 - Top Bracket</li> <li>48 - M8 Bolt</li> <li>48 - M8 Washer</li> <li>1 - M8 (13mm) Wrench</li> <li>1 - M6 (10mm) Wrench</li> <li>1 - Phillips Screwdriver</li> <li>32 - M6 Cage Nut</li> <li>32 - PVC Cup Washer</li> <li>32 - M6 Phillips Head Screw</li> <li>12 - Cable Management Hook</li> <li>12 - Hook Mounting Screw</li> <li>4 - Casters</li> <li>4 - Leveling Feet</li> <li>16 - M6 Screw</li> <li>16 - M6 Flat Washer</li> <li>16 - M6 Flange Nut</li> <li>4 - Grounding Wires</li> </ul>

Product appearance and specifications are subject to change without notice.