

# Datasheet

## Cartridge Fuse

RS Stock number 537-1600



### Specifications:

- Ratings above 6.3A have a maximum 0.81mm diameter lead
- Time-delay, high breaking capacity
- Ceramic tube, silver-plated endcap construction (500mA-800mA), nickel-plated brass endcap construction (1 – 12A)
- Optional sleeve is flexible flouropolymer (UL fammability rating VW-1).
- 5 x 20mm physical size
- Designed to IEC 60127-2 (500mA-10A) & extension 12A

S/N	Voltage Rating AC	Interrupting Rating @ Rated Voltage (50Hz) AC	Typical DC Cold Resistance ( $\Omega$ ) <sup>2</sup>	Typical Pre-arching	Typical Voltage Drop
5371600	250	1500	0.2370	0.632	189

### Dimensions - mm

