

Features

- Medium Duty
- Brake
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0631157



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Black rubber wheel 83 Shore A with zinc-chromium pressed steel material centre. Hub on roller bearing. In zinc-chromium plated pressed steel, turning on double rim of balls. Assembled with self-locking nut. Dust cover ring on the balls.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity (Kg)	205
Load Capacity / 4pcs (Kg)	820
Tyre Material	Rubber
Hub Material	Pressed Steel
Bracket Material	Pressed Steel
Includes Brake	Yes
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 80°
--	-------------

							
200x50	140x110	105x80	11x16	55	235	205	260

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	200
Wheel / Tread Width (mm)	50
Overall Height (mm)	235
Number of Fixing Holes	4
Fixing Hole Size (mm)	11x16
Hub Bearing Type	Roller Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	83
Levelling Extent (mm)	
Offset (mm)	55
Castor Weight (Kg)	3.869

Fixing Centres Specifications

Fixing Centres (mm)	140x110
Fixing Centres Length (mm)	140
Fixing Centres Width (mm)	110

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	105x80
Fixing Plate Length (mm)	105
Fixing Plate Width (mm)	80