

### General Information

Extended Product Type:	BAMH
Product ID:	1SNA114836R0000
EAN:	3472591148367
Catalog Description:	BAMH End Stops - Grey
Long Description:	BAMH End Stops - Grey - 9.1mm Spacing - G32, TH 35-7.5, TH 35-15 Rail

### Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Stops

### Ordering

EAN:	3472591148367
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

### Dimensions

Product Net Width:	9.1 mm
Product Net Height:	43 mm
Product Net Depth:	44.5 mm
Product Net Weight:	13 g

### Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	200 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	300 mm
Package Level 1 Gross Weight:	0.65 kg
Package Level 1 EAN:	3472591148367
Package Level 2 Units:	1000 piece
Package Level 3 Units:	24000 piece
Product Packing Type:	Bag

### Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

### Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

### Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Function:	End Stops
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BAMH
Product Name:	End Stop
Recommended Screw Driver:	5.5 mm
RoHS Date:	18 08 2005
Spacing:	9.1 mm
Suitable For:	131ETTM4TM4 D2.5/5.A.L.L D2.5/5.A.L.L.L D2.5/5.A.LLP.L D2.5/5.A.N.L D2.5/5.A.N.L.L D2.5/5.A.NLP.L D2.5/5.A.NLP.L.L D2.5/5.D2.L D2.5/5.DD.L D2.5/5.DE.L D2.5/5.DE1.D.L D2.5/5.DE1.L

D2.5/5.DE2.D2.L  
D2.5/5.DE2.L  
D2.5/5.DL.L  
D2.5/5.L.L  
D2.5/5.LL.L  
D2.5/5.LLP.L  
D2.5/5.N.L  
D2.5/5.NL.L  
D2.5/5.NLP.L  
D2.5/5.NTLP.L  
D2.5/5.T1.L  
D2.5/5.T1.P.L  
D2.5/5.T3.L  
D2.5/5.T3.P.L  
D4/6.A.LL  
M120/35.AF  
M120/35.F  
M120/35.FF  
M300/42.AF  
M300/42.F  
M300/42.FF  
M35/26.AF  
M35/26.F  
M35/26.FF  
M70/31.AF  
M70/31.F  
M70/31.FF

**Tightening Torque:** acc. IEC 60947-1 0.8 N·m  
Manufacturer 1 N·m

---

### Certificates and Declarations (Document Number)

**RoHS Information:** 1SND230479F0202

---

### Classifications

**E-nummer:** 2925485  
**ETIM 4.0:** EC001041 - End bracket for terminal block  
**ETIM 5.0:** EC001041 - End bracket for terminal block  
**Object Classification Code:** X

