

Specifications

Eaton 5P650IRG2BS

Eaton 5P Gen2 UPS, 650 VA, 520 W, Input: C14, Outputs: (4) C13, Rack, 1U, BS Input cord



General specifications

PRODUCT NAME	Eaton 5P Gen2 UPS
CATALOG NUMBER	5P650IRG2BS
EAN	3553340710469
PRODUCT LENGTH/DEPTH	361 mm
PRODUCT HEIGHT	43.2 mm
PRODUCT WIDTH	438 mm
PRODUCT WEIGHT	8.863 kg
WARRANTY	3 year on electronics, 2 year on battery
COMPLIANCES	LVD Directive (CB) EMC Directive RoHS Directive WEEE Directive Packaging Directive Batteries Directive
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 IEC/EN 62040-3 UL 1778 CSA-C22.2 CE UKCA Cm Ukr KCC cTUVus BIS

Battery

BATTERY TYPE	Lead-acid maintenance-free (replaceable)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY REPLACEMENT	User replaceable
BATTERY QUANTITY	2
BATTERY MANAGEMENT	ABM or constant voltage charging method (user selectable), automatic battery test, deep discharge protection
BATTERY RATING	6 V / 9 Ah
EXTENDED BATTERY	No

Electrical output

RECEPTACLE	(4) C13
VOLTAGE	230V
WATTAGE	520
OUTPUT POWER FACTOR	0,8
OUTPUT VOLTAGE RANGE	230 V (+6%/-10%)
OUTPUT WAVEFORM	Sine wave
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
TOPOLOGY	Line-interactive

CAPABILITY	
-------------------	--

Electrical input	
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50-60 Hz
INPUT VOLTAGE RANGE	160-294 V (adjustable to 150 V-294 V)
INPUT FREQUENCY RANGE	47-70 Hz (50 Hz system), 56.5-70 Hz (60 Hz system), 40 Hz in low sensitivity mode

Environmental	
ALTITUDE	3000 m
NOISE LEVEL	<35 dB at 1 meter
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
RELATIVE HUMIDITY	0-90% non-condensing

Resources	
APPLICATION NOTES	Runtime graph - 5P650IRG2
BROCHURES	Eaton 5P Gen2 UPS datasheet

VA RATING	650 VA
------------------	--------

Communications	
INCLUDES NETWORK CARD	No
COMMUNICATION	<ul style="list-style-type: none"> • USB port (HID compliant) • Serial port (RS232) • Mini-terminal block for remote On/Off and Remote Power Off • Dry contacts (2 outputs, optocoupler, RJ)
ETHERNET INTERFACE	No
USER INTERFACE	Multilingual graphical LCD display
POTENTIAL FREE SWITCH CONTACT	Yes
EXPANSION SLOTS	One slot for optional communication card
SOFTWARE COMPATIBILITY	Eaton Brightlayer Software suite
TYPE OF INTERFACE	Other

Additional specifications	
CONSTRUCTION TYPE	482.6 mm (19 inch) device
ENCLOSURE	Black/silver
PACKAGE CONTENTS	<ul style="list-style-type: none"> • Rack-mounting kit • Cable locking system • USB cable • (2) IEC-IEC cables • Quickstart guide • Safety instructions • BS Input cord
PHASE (OUTPUT)	1
AUTO SHUTDOWN FUNCTION	Yes
COLOR	Black/silver
EFFICIENCY	97
RACK MOUNTING KIT	Yes
PHASE (INPUT)	1

DECLARATIONS OF CONFORMITY	EU Declaration of conformity Eaton 5P Gen2 UPS
MANUALS AND USER GUIDES	Eaton 5P Gen2 Quick Start Guide Eaton 5P Gen2 Rack - Advanced user guide

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

