


PRODUCT-DETAILS

216BS4

Surface inlet, 4h, 16A, IP44, 2P+E



General Information

Extended Product Type	216BS4
Product ID	2CMA193289R1000
EAN	7392696932899
Catalog Description	Surface inlet, 4h, 16A, IP44, 2P+E
Long Description	Wall mounted inlet, earthing sleeve position 4h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Yellow

Ordering

E-Number (Sweden)	E2417161
E-Number (Finland)	2420041
E-Number (Norway)	1542361
EAN	7392696932899
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	65 mm
Product Net Height	66 mm

Product Net Weight	0.15 kg
Mechanical Drawings	9AKK107680A3028

Container Information

Package Level 1 Width	138 mm
Package Level 1 Depth / Length	158 mm
Package Level 1 Height	345 mm
Package Level 1 Gross Weight	1.5 kg
Package Level 1 EAN	739269662895
Package Level 1 Units	box 10 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	1010 kg
Package Level 2 EAN	7392696080194
Package Level 2 Units	pallet (lift) 660 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	2CHC660161X0201
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	18 mm
Color	Yellow
Connection Type	Screw
Degree of Protection	IP44
Design	Surface mounted plug
Frequency (f)	50 Hz 60 Hz
Function	Wall mounted inlet

Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#216BS4
Mounting Holes	75x54
Mounting Type	Angled
Number of Poles	3
Order Multiple	10 piece
Product Main Type	EBS
Product Name	Wall mounted inlet
Protection Type	Splashproof
Rated Current (I_n)	16 A
Rated Frequency (f)	50 ... 60 Hz
Rated Voltage (U_r)	100 ... 130 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Surface Inlets
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440519
UNSPSC	39121406

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Inlets for Panel Mounting

