

PRODUCT-DETAILS

TC814-TB

MINI MTG BASE .8X.4IN NAT NY SCREW



General Information

Extended Product Type	TC814-TB
Product ID	7TAG009880R0011
EAN	5414363075059
Catalog Description	MINI MTG BASE .8X.4IN NAT NY SCREW
Long Description	Miniature Screw-Mounted Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.3mm (0.76 Inches), Width of 9.78mm (0.385 Inches), Height of 5.0mm (0.197 Inches), Screw Mounting Method, #5 Screw, Mounting Hole Diameter of 3.3mm (0.130 Inches)

Ordering

EAN	5414363075059
UPC	786210826288

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	10.75 in 273 mm
Package Level 2 Height	10.5 in 267 mm
Package Level 2 Depth / Length	12.75 in 324 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19670831
Material	Nylon/Polyamide 6.6
Mounting Holes	#5
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Mounting Base
Special Functions	A standard two-hole base that installs in-line with the wire bundle which conceals it.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC814-TB
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC814-TB
REACH Declaration	9AKK107992A3995
RoHS Information	9AKK107992A8806

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

