

D 19 TMU-10

Socket set 1/2"

25 pieces

Code
6151960

ETIM
EC002209

EAN
4010886615195

UNSPSC
27-11-17-03

Country of origin
Germany

eCl@ss
21-04-02-05

Customs tariff number
82042000



12,5 1/2" mm

Article description

- With forged, tempered hexagon (No. 19) or bi-hexagon (No. D 19) UD profile sockets, hand-operated
- With accessories made from vanadium steel 31CrV3
- With robust lever-change reversible ratchet, with push-button release
- In GEDORE blue sheet steel case
- Dimensions: 425 x 277 x 55 mm

Article parts list

Ratchet, 1993 U-10 T, Inserts, D 19 10 11 12 13 14, 15 16 17 18 19 21 22, 23 24 26 27 28 30 32, Accessories, 1/2" crank 1985, 1/2" crosshandle with sliding block 1987, 1/2" extension 1990-5-10, Cardan joint 1995

Article information

Contents (Qty of pieces)	25	Total height [mm]	57 mm
Net weight [kg]	6,6 kg	Total depth [mm]	277 mm
Total length [mm]	425 mm	Drive connector square (male)	1/2"
Total width [mm]	280 mm	Drive connector square (male)	12,5 mm