
VDE Screwdrivers



Insulation directly injection-moulded around the blade according to EN60900

Ergonomic, shock resistant, anti slip handle and for greater torque to be applied with less effort

Each screwdriver is individually tested to 10,000V in a water bath for 10 SCEa

Hardness and torque values exceed ISO/DIN standards

Part No.	Length (mm)	Tip Size (mm)
65-966	Std Parallel 3mm x 100mm	0.5 x 3.0
65-967	Std Parallel 4mm x 100mm	08 x 4 0
65-968	Std Parallel 5.5mm x 125mm	1.0 x 5.5
65-969	Std Parallel 6.5mm x 150mm	1.2 x 6.5
65-970	Std Parallel 8mm x 175mm	1.6 x 10.0
65-971	Std Parallel 10mm x 200mm	-
65-972	Phillips®#0PH x 60mm	-
65-973	Phillips®#1 x 80mm	-
65-974	Phillips®#2 x 100mm	-
65-975	Phillips®#3 x 150mm	-