

MARQUARDT

SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

T0 12 (4) A 250 V AC

single-pole	18 01.63 25	18 01.13 02	18 01.13 03	18 01.62 22	18 01.12 02	18 01.22 02	18 03.11 21	18 03.21 02	18 03.24 02	18 03.25 03	18 03.51 02	18 03.61 21	18 03.61 52
	Normally closed contact (SPNC)			Normally open contact (SPNO)			Switch (SPDT)						
Voltage lamp in V													
Actuator color / printing													
Housing color													
12 (4) A 250 V AC 1E4													
10 (4) A 250 V AC 1E4	•			•			•	•	•	•	•	•	•
8 (8) A 250 V AC 5E4													
6 (4) A 250 V AC 5E4	•			•			•	•	•	•	•	•	•
6 (2) A 250 V AC 1E4													
4 (3) A 250 V AC 6E3													
4 (2) A 250 V AC 1E4		•	•		•	•							
30 mA 12 V 5E4													
30 mA 12 V DC 5E4													•
15 A 250 V AC 1 1/2 HP													
15 A 125 V AC 3/4 HP													
10 A 250 V AC 1/2 HP	•			•			•					•	
10 A 125 V AC 1/3 HP	•			•			•					•	
6 A 250 V AC 1/2 HP								•	•	•	•		
6 A 125 V AC 1/4 HP								•	•	•	•		
6 A 125 - 250 V AC 1/8 HP													
6 A 125 V AC 1/10 HP		•	•		•	•							
4 A 250 V AC 1/10 HP		•	•		•	•							
Connection type	U	U	U	U	U	U	U	U	U	U	J	U	U
Connection description		4.8	4.8		4.8		4.8						
Inrush current in A (capacitive)													
Contact distance in mm	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag
EN 60335 cap. 30 conform *G*													
Miscellaneous									Installation depth 13.2	Installation depth 16.2			
Stock version		•		•	•	•	•	•	•		•	•	•