

Slimstar-10, 30 and 50 PIR

**Mains
Powered**



10w

30w

50w

- A PIR Sensor (passive infrared sensor) - Automatically lights up when motion is detected, making it an ideal lighting solution for security purposes.
- 1,000, 3,000 and 5,000 lumens with a 10, 20 or 30 metre shadow free flood beam
- Long Life: High performance LED SMD technology operating for 50,000hrs
- Low Cost: Uses up to 80% less power than Halogen models, it is safe for both indoor and outdoor use.
- Cool running: Safe for use in confined spaces as it contains no Mercury or Hazardous materials.
- Construction: Die-cast aluminium housing with durable powder coated finish with an adjustable mounting bracket, stainless steel fittings and 300mm Flex.
- The PIR sensor has an adjustable mounting bracket and stainless steel fixings.

- 1000
3000
5000
Lumens
- 10-30m
Flood Beam
Distance
- LED
SMD
Technology
- 120°
120° beam
angle
- 50,000 hour
lifetime
- 180° PIR
Detection

Specifications

Light Output	1000, 3000 or 5000
Light Beam	10,20 or 30 Metre flood beam
Voltage	85v-265v AC, 50-60Hz
Beam Angle	120° beam angle
Product Dimensions (Max.)	(L)296mm (W)240mm (D)40mm
LED	SMD LED (up to 50,000hrs of light)
Product Weight	752g, 980g or 1.2Kg
Weather Resistance	Water and dust resistant to IP65 rating
Luminous efficacy	90-100lm/W
PIR Sensor	PIR Sensor has a 180° detection
Cable	300mm flex
Part No.	NSSLIMSTAR10PIR NSSLIMSTAR30PIR NSSLIMSTAR50PIR

