PLT13H-Q0






- Greater resistance to damage caused by ultraviolet light indoor or outdoor use
 - Versatile cable ties can be used in countless applications
 - One-piece construction for consistent performance and reliability
 - Lowest threading force of any one-piece cable tie in the industry
 - Curved tip on Standard cross section is easy to pick up from flat surfaces and allows faster initial threading to speed installation. Light-Heavy and Heavy cross section is a straight tip design

■ Part Number	PLT13H-Q0
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie, 43.3", Heavy cross section
■ Product Type	Cable Ties
■ Material	Weather Resistant Nylon 6.6
■ Color	Black
 CSA Certified 	No
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	No
■ Length (In.)	43.3
■ Length (mm)	1100
■ Width (In.)	.350
■ Width (mm)	8.9
■ CE Compliant	Yes
Cross Section	Heavy
■ Head Height (In.)	.340
■ Head Height (mm)	8.6
■ Head Width (In.)	.560
■ Head Width (mm)	14.2
■ Locking Style	Locking
 Material Flammability Rating 	UL 94-HB
■ Max. Bundle Diameter (In.)	13.00
■ Max. Bundle Diameter (mm)	330
 Max. Continuous Use Temperature 	e 185°F (85°C)
Min. Loop Tensile Strength (Lbs.)	175
■ Min. Loop Tensile Strength (N)	778

■ Pricing Description	Cable Tie, 43.3"L (1100mm), Heavy, Weather Resistant, Black
■ Thickness (In.)	.078
■ Thickness (mm)	2.0
■ Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
■ Min. Order UOM	PC
■ Min. Order Qty.	25
■ BOM Qty. (# of Pkgs.)	



PANDUIT * PART NO.	BUNDL in MIN. (mm)	in		B in (mm)	C in (mm)	in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE 1bs.	CROSS SECTION	T I P STYLE	WEIGHT bs./100 pcs. (g)
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.358 (9.1)	.290 (7.4)	.480 (12.2)	8.1 (206)	120 (534)	HEAVY	STRA I GHT	.76 (346)
PLT2.5H	.188	2.50 (64)	.075 (1.9)	.300 (7.6)	.358 (9.1)	.290 (7.4)	.480 (12.2)	9.8 (251)	120 (534)	HEAVY	STRA I GHT	.90 (408)
PLT3H	.188	3.00 (76)	.075 (1.9)	.300 (7.6)	.358 (9.1)	.290 (7.4)	.480 (12.2)	11.4 (290)	120 (534)	HEAVY	STRAIGHT	1.04 (472)
PLT4H	.188	4.00 (102)	.075 (1.9)	.300 (7.6)	.358 (9.1)	.290 (7.4)	.480 (12.2)	14.5 (368)	120 (534)	HEAVY	STRA I GHT	1.28 (581)
PLT5H	.188	5.00 (127)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	17.7 (450)	175 (778)	HEAVY	STRA I GHT	2.06 (934)
PLT6H	.188	6.00 (152)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	20.9 (530)	175 (778)	HEAVY	STRAIGHT	2.46 (1116)
PLT8H	.188	9.00 (229)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	30.6 (779)	175 (778)	HEAVY	STRA I GHT	3.36 (1524)
PLT13H	5.50 (140)	13.00	.078 (2.0)	.350	.406 (10.3)	.340 (8.6)	.560 (14.2)	43.3 (1100)	175 (778)	HEAVY	STRAIGHT	4.59 (2080)

NOTES:

1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. *2) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

SS_5540_00.PRT

								DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS							
										PAN	CORP. TINLEY PARK, ILLINOIS				
										Р	PAN-TY CABLE TIES PLT SERIES				
										DIMENSION	HERWISE SPECIFIED, AL TOLERANCES ARE: (.XXX) ± .020(.51) .02(.5)ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJEC	CTION.		
										DRAWN BY SO	MAT'L:	SCALE NONE			
7	7/3/03	JABO		ADDED C REF DIMENSION TO TIE. C DIM. WAS ALREADY IN MATRIX.	5540	7				DATE 12-27-84	NYLON 6/6	SS-5540	DWG		
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP	·	HVP		SHEET 4	SIZE		