

# CUAL EK 562813 G 2X150mm2



Sample image

**Order symbol :** CUAL EK 562813 G 2X150mm2

**EAN :** 6418074319722

**Product nr :** 2674643

**El. number :**

**Description :** Terminal enclosure

- Finland : 3424737
- Denmark : 8212052903
- Sweden : 2674643

2674643\_FIBOX\_CUAL\_EK\_562813\_G\_2x150mm2\_DIM

| Dimensions : | Height | Width | Depth |
|--------------|--------|-------|-------|
| mm :         | 560    | 280   | 130   |
| inch :       | 22.05  | 11.02 | 5.12  |

## Materials :

|                   |                      |
|-------------------|----------------------|
| Material :        | Polycarbonate        |
| Base colour :     | RAL_7035             |
| Cover colour :    | RAL 7035 -light grey |
| Gasket material : | Polyurethane         |

## Temperatures :

|                               |             |
|-------------------------------|-------------|
| Temperature °C (continuous) : | -40 ... 80  |
| Temperature °F (continuous) : | -40 ... 175 |

## Ratings :

|                                         |                   |
|-----------------------------------------|-------------------|
| Ingress protection (EN 60529):          | IP66; IP67;       |
| Impact Resistance (EN 62262):           | IK08;             |
| electrical_insulation :                 | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815) : | Yes               |
| UV resistance :                         | UL 746C           |
| Flammability Rating :                   | UL 94 V0          |
| Glow Wire Test (IEC 695-2-1) °C :       | 960C              |