



General characteristics

Uprights:

"C" Profile 50x30x15x1.5 mm perforated every 62.5 or 31.25 mm.

Load capacity: up to 2500 kg per bay.

Shelves:

All the shelves are of tubular design with 4 upright-connectors and 2 clamps for the 250 kg version and 3 clamps for the 500 kg version.

- **Tubular, 250 kg version:** one piece made from welded tubes 20x20 mm. Particularly suitable for high-bay storage and multi-level installations.
- **Tubular, 500 kg version ¹²:** one piece made from welded tubes 35x20 and 20x20 mm.
- **Steel sheet ¹³:** steel sheet folded and welded on the 500 kg tubular version.
- **Mesh ¹⁴:** 50x50 mm with 3 mm diameter wire welded under the tubular 500 kg version. Ideal for storage in warehouses fitted with sprinkler systems. Also maintain the brightness in the warehouse. Avoid the accumulation of dust. Shelf load capacity: up to 500 kg per level depending on the configuration.

Shelf covers:

- Natural hardboard 2.5 mm thick.
- Galvanised steel sheet 0.8 mm thick.
- Chipboard 8 mm thick.

Accessories:

- Plastic feet.
- Welded metal feet.
- Galvanised metal feet 110x50x3 mm.
- Side cross brace.
- Stops (*central, front/back, sides*) see Flip accessories.
- Back walls and side panels.
- Safety pins.

Finish:

Epoxy powder coated in the standard RAL 5015 blue.

