

Plugs / Converters

Euro Converter White Non Returnable 3A



Technical Specification

Product Code	ECP-WNR-3A
Feature 1	Converts 2.5A Europlug and German Schuko to 13A BS type
Feature 2	Clips in 13A Euro converter plug terminals quickly and securely
Feature 3	1 Year Guarantee
Approval body	BSI
Barcode	5012739618628
Colour	Black
Company DUNS Number	216156018
Country of Origin	China
Current (I)	3
Finish body	Mat

Tel No: 01279 772 772

Email: sales@greenbrook.co.uk

Website: www.greenbrook.co.uk

Frequency (Hz) max	60
Frequency (Hz) min	50
Greenbrook Guarantee (Years)	1
HS Code	8536699099
Ingress Protection (IP)	20
Installation method	Plug convertor
Materials Main Body	Nylon
Min Order Qty	1
Operating Temperature Range max C	70
Operating Temperature Range min C	-5
Pack Contents	1
Package Product Max. Length (mm)	550
Package Product Max. Height (mm)	315
Package Product Max. Width (mm)	275
Package Product Weight gross (g)	10595
Product Weight net (g)	36
Sales Pack Qty	1
Standards	BS 5733, BS 1363
StatusCode	Active
Voltage (VAC) MAX (V)	240
Voltage (VAC) Min (V)	220
Voltage (VAC) Rated (V)	230
Wattage (W)	700

Tel No: 01279 772 772

Email: sales@greenbrook.co.ukWebsite: www.greenbrook.co.uk