



## 3114 - FEMALE STUD FITTING WITH BSPP AND METRIC THREAD



<b>maximum working pressure</b>	20 bar 2 MPa 290 psi
<b>working temperature</b>	-20 to 80 °C -4 to 176 °F 253 to 353 °K
<b>vacuum capability</b>	755 mm Hg
<b>body</b>	NICKEL PLATED BRASS
<b>'O'-rings</b>	NBR
<b>gripping ring</b>	STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	H (mm)	(kg)
	All ▼	All ▼	All ▼	All ▼	All ▼	All ▼
3114 04 10	4	G1/8	9.5	13	22.5	.01
3114 04 13	4	G1/4	13.5	16	26.5	.015
3114 04 19	4	M5x0,8	6.5	8	19.5	.005
3114 06 10	6	G1/8	9.5	13	24.5	.011
3114 06 13	6	G1/4	13.5	16	28.5	.016
3114 08 10	8	G1/8	9.5	13	29	.015
3114 08 13	8	G1/4	13.5	16	33	.021
3114 08 17	8	G3/8	14	19	34	.025
3114 10 13	10	G1/4	13.5	16	36	.027
3114 10 17	10	G3/8	14	19	36	.026
3114 10 21	10	G1/2	19.5	24	41.5	.047
3114 12 17	12	G3/8	14	19	40	.033
3114 12 21	12	G1/2	19.5	24	45.5	.053
3114 14 17	14	G3/8	14	22	42.5	.057
3114 16 21	16	G1/2	15	27	49	.096