



Main

Range	PanelSeT
Offer type	Spare part
Accessory / separate part category	Enclosure accessory
Product or component type	Roof
Device application	Multi-purpose
Range compatibility	PanelSeT PanelSeT SF suitable enclosure
Device composition	1 roof




Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - screw type M12 - roof fixing point location By screws - screw type M6 - roof fixing point location
Height	7.5 Mm
Width	1196 Mm
Depth	396 Mm
Thickness	1.5 Mm
IP degree of protection	IP55 conforming to IEC 60529 (enclosure protection)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 Cm
Package 1 Width	81.000 Cm
Package 1 Length	127.000 Cm
Package 1 Weight	7.508 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	15
Package 2 Height	78.000 Cm
Package 2 Width	100.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	126.320 Kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	No

Contractual warranty

Coverage	Core product
----------	--------------