

FEATURES

- 50 Ω impedance
- Operating frequency is 11GHz
- Nickel body plating and gold plated contact

RS PRO N Plug to BNC Socket

RS Stock No.: 2177794



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These coaxial type adapters are designed to provide an efficient means of connecting coaxial cable assemblies through panel mount connections.

These connectors are made of industry standard components and are most commonly used to connect radio and television broadcast equipment.

RS Pro straight N plug to BNC socket type RF adapter features silver body plating and gold plated contact. This N plug to BNC socket type RF adapter has 50Ω impedance.

General Specifications

Type of coaxial connector	N Plug to BNC Socket
Body Plating	Nickel
Termination method	Cable
Contact Material	Brass
Contact Plating	Nickel
Gender A	Plug
Gender B	Socket
Mounting type	Panel mount

Electrical Specifications

Temperature Range	-65° ~ +165°
Characteristic Impedance	50Ω
Frequency Range	0~11GHz
Working Voltage	1000V
Insulation Resistance	≥1000MΩ
Medium Pressure	1000V(rms)
VSWR	≤1.3
Working Life	500Cycles

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5462453	RS PRO	RF Adapter	50Ω impedance	Operating frequency is 11GHz	

