



Main

Range	Resi9
Product or component type	Cover set
Range compatibility	Opale Resi9
Cabling installation system	Housing wall trunking
Number of 18 mm modules per row	18
Fixing mode	Stapled
Standards	NFC 15-100 NF EN 50085-2-1

Complementary

Material	Plastic
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
Provided equipment	1 cover (18
Ambient air temperature for operation	-15...60 °C
IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Height	2600 mm
Width	357 mm
Depth	64 mm
Colour tint	White (RAL 9003)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations