

**Part Number :** [190750003](#)

**Product Description :** InsulKrimp Star Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4)

**Series Number :** 19075

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Number :** SRA-229-08X



---

## Documents & Resources

### Drawings

[190750003\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19075
Description	InsulKrimp Star Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4)
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal
UPC	800753079403

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.642/g

Packaging Type	Bag
Stud Size	8 (M4)
Wire Insulation Diameter	3.68mm
Wire Size (AWG)	18, 20, 22

---

## Application Tooling

### Global

Description	Part Number
Hand Crimp Tool	<u>640010500</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050500</u>

---

This document was generated on Sep 23, 2025