

# 3GAA091500-ASJ



## General Information

Product ID:	3GAA091500-ASJ
ABB Type Designation:	M3AA 90L 2
Catalog Description:	No Description Available

## Additional Information

ABB Type Designation:	M3AA 90L 2
Bearing:	6205-2Z/C3
Bearing NDE:	6204-2Z/C3
Country of Origin:	China (CN) Finland (FI) Romania (RO) Poland (PL)
Customs Tariff Number:	85015220
Direction of Rotation:	Both sides

### Electrical Data:

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.50 kW	2900 r/min	3.00 A	0.860	84.40 %	4.90 N·m	6.70
D	--	50 Hz	230 V	1.50 kW	2899 r/min	5.20 A	0.860	84.40 %	4.93 N·m	6.70
Y	--	50 Hz	415 V	1.50 kW	2909 r/min	2.90 A	0.850	84.40 %	4.90 N·m	7.20

Gross Weight:	19 kg
IC Class:	IC411
IE Class Data (50 Hz):	IE Class IE3 Full Load (100%) 84.2 % Partial Load (75%) 84.2 % Partial Load (50%) 82.1 %
IM Class:	IMB3 IM1001
IP Class:	IP55
Insulation Class:	ICLF
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Package Level 1 Units:	0 carton
Poles (High):	2
Product Name:	3-Phase squirrel cage motor
Product Net Weight:	16 kg
Quote Only:	No
Replaced Product ID (OLD):	3GAA091612-ASJ
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Nordic Central Stock Spain CSI
Temperature Class Default:	--
Terminator Box Location:	D-End top
Two Speed Motor:	No
Voltage Code:	S